

## PROFINET avec les contrôleurs SIMATIC (TIA Portal) (IK-PNCOM)

---

### Short Description

---

PROFINET gives you new ways to boost your productivity with four key advantages – openness, flexibility, efficiency, and performance. This course teaches you the versatile possibilities of PROFINET – the leading Industrial Ethernet standard for automation – for networking your plant and enables you to realize efficient real-time communication with SIMATIC Controllers.

### Objectives

---

In this course you will learn to use the real-time-capable standard PROFINET in your automation solution. You will learn how to parameterize, commission, diagnose and troubleshoot a PROFINET network quickly and effectively. Numerous practical exercises with SIMATIC and SCALANCE products and TIA Portal reinforce the acquired theoretical knowledge.

### Target Group

---

- Engineering personnel
- Programmers
- Commissioning engineers

### Content

---

- Basics of PROFINET
- Configuring PROFINET IO
- Configuring topologies
- Device and network diagnostics
- Ring redundancy (MRP)
- Shared device
- I device
- Isochronous realtime communication (IRT)
- Gateways and communication via PN/PN couplers

### Prerequisites

---

SIMATIC S7 knowledge according to the course TIA-PRO1, TIA-SERV2 or TIA-SYSUP.

### Note

---

Course documentation: French  
Instructor: French

### Type

---

Face-to-face training

### Duration

---

3 days

### Language

---

fr