

SINAMICS SH150 - Diagnostics and Service (DR-SH15-DG)

Objectives

You are responsible for service work and maintenance of medium-voltage converters.

In this course you will learn how the SINAMICS SH150 converter works in the circuit technology of modular multi cells M2C.

After the course you will be able to read and understand operating parameters. In the event of a fault, you can carry out a target-oriented troubleshooting and recommissioning. For this purpose, you will also be able to back up data using the STARTER PC program.

Target Group

Service personnel

Maintenance personnel

Content

Design and function of the SINAMICS SH150:

- Principle of the inverter in different circuits
- Rectifier, inverter, DC-link and precharging
- Inverter in modular multi cell design M2C

Operation and diagnostics with Operator Panel TP900

Operation and diagnostics with PC program STARTER

Data backup:

- Upload and download of parameter sets
- Comparison of parameter sets

Reading and understanding circuit diagrams:

- Input and output signals, setpoint channel
- Control with CU320-2 and actual value measurements
- Interface to PROFIBUS / PROFINET

Diagnostics and troubleshooting:

- Checking the control and status signals
- Analysis of alarm and error messages
- Signal recording via trace function

Test functions after replacement of spare parts

Work safety on medium-voltage installations

Practical exercises on special training equipment

Prerequisites

Knowledge of electrical drive technology

Knowledge of SINAMICS or STARTER is not required

Note

During the course you will work on special training equipment and partly on original equipment, adapted to low voltage (400 V) for your safety.

An introduction to the complete system and its operation under medium voltage (> 1000 V) is not covered by the course. This is usually done on site by personnel with the appropriate experience.

For customer-specific courses, please let us know the application in advance, such as 4-quadrant drive, grid feed, grid coupling or grid compensation.

Type

Face-to-face training

Duration

5 days

Language

en