

SINAMICS G120 Oppstart og Service (DR-G12-PM)

Short Description

Learn to parameterize and commission the drive SINAMICS G120. You will get an overview of SINAMICS G120, how to commission it with STARTER, how to set control and status word. You will learn to integrate SINAMICS G120 in SIMATIC, how to run diagnostics and use safety functions

Objectives

SINAMICS G120 allow the variable-speed operation of induction motors to drive pumps, fans, conveyor systems and many other machines. This course shows you how to handle the SINAMICS G120 inverter using Software Startdrive within the TIA Portal. After the course you are able to be correctly commission the inverter and adapt it to address the particular application. You know suitable inverter functions and parameter settings for a wide range of applications. You can make a data backup, and taking the appropriate measures when faults occur.

Target Group

Commissioning engineers
Service personnel

Content

Design and principle of operation of the SINAMICS G120 inverter with:

- Control Unit CU
- Power Module PM

Parameterization, data backup and diagnostics with:

- BOP-2 and IOP operator panels
- Software Startdrive in TIA Portal

Setpoint channel and closed-loop control
Control signals and signal interconnections

Inverter functions

Practical exercises using the training device with:

- SINAMICS CU240E-2 PN with PM 240 FS A
- SIMOTICS induction motor

Prerequisites

Basic knowledge of electrical engineering

Note

Documentation in English.
Register in the calendar one week before the training starts.

Type

Face-to-face training

Duration

2 days

Language

no

Fee

15,400 NOK