

PROFINET with SIMATIC Controllers (TIA Portal) (IC-PNCOM)

Kort beskrivning

PROFINET gives you new ways to boost your productivity with four key advantages – openness, flexibility, efficiency, and performance. This course teaches you the versatile possibilities of PROFINET – the leading Industrial Ethernet standard for automation – for networking your plant and enables you to realize efficient real-time communication with SIMATIC Controllers.

Beskrivning/mål

In this course you will learn to use the real-time-capable standard PROFINET in your automation solution. You will learn how to parameterize, commission, diagnose and troubleshoot a PROFINET network quickly and effectively. Numerous practical exercises with SIMATIC and SCALANCE products and TIA Portal reinforce the acquired theoretical knowledge.

Målgrupp

- Engineering personnel
- Programmers
- Commissioning engineers

Innehåll

- Basics of PROFINET
- Configuring PROFINET IO
- Configuring topologies
- Device and network diagnostics
- Ring redundancy (MRP)
- Shared device
- I device
- Isochronous realtime communication (IRT)
- Gateways and communication via PN/PN couplers

Förkunskaper

SIMATIC S7 knowledge according to the course [TIA-PRO1](#), [TIA-SERV2](#) or [TIA-SYSUP](#).

Typ

Utbildning

Antal dagar

3 dagar

Språk

en