

SINAMICS S120 - Diagnostics at Chassis- and Cabinet Units (DR-S12-CHA)

Ziele

You are responsible for reliable operation of the SINAMICS S120 drives with power ratings exceeding 100 kW. You already know the system from the booksize format with its modular structure.

In this course you will learn how to handle chassis units and cabinet units. The focus is on understanding the converter design and the differences with respect to the booksize format.

After the course, you will be able to go about resolving faults in a targeted way. By means of circuit diagrams, you will be able to identify and determine interfaces and replace components. Using the AOP30, you will be able to back up data and recommission the drive system.

Zielgruppe

Commissioning engineers

Service personnel

Maintenance personnel

Inhalte

Design and circuit diagrams of SINAMICS S120 chassis units with power ratings above 200 kW

Design and circuit diagrams of the modular SINAMICS S120 CM cabinet units

Working with the AOP30 Advanced Operator Panel

- Access to parameters and interfaces

- Diagnostics, data backup and recommissioning

Working on the converter when service is required:

- Power Block diagnostics using measuring devices

- Replacing electronic modules and installing replacement parts

- Replacing the Power Block

Special features of liquid-cooled SINAMICS S120 LC units

Special features of the SINAMICS S150 cabinet unit

Practical exercises carried out on chassis and cabinet units with troubleshooting, component replacement and recommissioning

Teilnahmevoraussetzung

Good knowledge of SINAMICS in accordance with the courses on commissioning DR-S12-PM (formerly DR-SNS-SI) or maintenance DR-S12-DG (formerly DR-SNS-IH).

Hinweise

This course is also suitable for participants involved in commissioning work.

This course has been specifically designed for SINAMICS S120 users. If you have already participated in a SINAMICS G150 training course, then you have comparable knowledge regarding chassis and cabinet units

Typ

Präsenztraining

Dauer

3 Tage

Sprache

en