

## SINAMICS G120 - Parameterizing and Commissioning (DR-G12-PM)

---

### Short Description

---

In this course you learn to commission the inverter and adapt the parameters. You can make a data backup, and taking the appropriate measures when faults occur.

[Also available as online-training](#)

### Objectives

---

SINAMICS G120 allow the variable-speed operation of induction motors to drive pumps, fans, conveyor systems and many other machines. This course shows you how to handle the SINAMICS G120 inverter using Software Startdrive within the TIA Portal. After the course you are able to be correctly commission the inverter and adapt it to address the particular application. You know suitable inverter functions and parameter settings for a wide range of applications. You can make a data backup, and taking the appropriate measures when faults occur.

### Target Group

---

Commissioning engineers  
Service personnel

### Content

---

Design and principle of operation of the SINAMICS G120 inverter with:

- Control Unit CU
- Power Module PM

Parameterization, data backup and diagnostics with:

- BOP-2 and IOP-2 operator panels
- Software Startdrive in TIA Portal

Setpoint channel and closed-loop control

Control signals and signal interconnections

Inverter functions

Practical exercises using the training device with:

- SINAMICS CU240E-2 PN with PM 240 FS A
- SIMOTICS induction motor

### Prerequisites

---

Basic knowledge of electrical engineering

### Note

---

none

### Type

---

Face-to-face training

### Duration

---

2 days

### Language

---

en