

## PROFINET with SIMATIC Controllers (TIA Portal) (IK-PNCOM)

---

### Short Description

---

PROFINET gives you new ways to boost your productivity with four key advantages – openness, flexibility, efficiency, and performance. This course teaches you the versatile possibilities of PROFINET – the leading Industrial Ethernet standard for automation – for networking your plant and enables you to realize efficient real-time communication with SIMATIC Controllers.

### Objectives

---

In this course you will learn to use the real-time-capable standard PROFINET in your automation solution. You will learn how to parameterize, commission, diagnose and troubleshoot a PROFINET network quickly and effectively. Numerous practical exercises with SIMATIC and SCALANCE products and TIA Portal reinforce the acquired theoretical knowledge.

### Target Group

---

Engineering personnel  
Programmers  
Commissioning engineers

### Content

---

Basics PROFINET  
Configuring PROFINET  
Configuring topologies  
Device and network diagnostics  
Ring redundancy (MRP)  
Shared Device  
I-Device  
Cycle synchronicity with PROFINET IRT  
Gateways and communication via PN/PN couplers

### Prerequisites

---

SIMATIC S7 knowledge according to the course TIA-PRO1, TIA-SERV2 or TIA-SYSUP.

### Type

---

Face-to-face training

### Duration

---

4 days

### Language

---

sv

### Fee

---

24,600 SEK