

SINAMICS G120 Parameterizing and Commissioning Course (DR-G12-PM)

Short Description

SINAMICS G120 allow the variable-speed operation of induction motors to drive pumps, fans, conveyor systems and many other machines. This course shows you how to handle the SINAMICS G120 inverter.

Objectives

After the course you are able to correctly commission the inverter and adapt it to address the particular application. You will know suitable inverter functions and parameter settings for a wide range of applications. You can make a data backup, and taking the appropriate measures when faults occur.

Target Group

Commissioning engineers
Service personnel

Content

Design and principle of operation of the SINAMICS G120 inverter with:

- Control Unit CU
- Power Module PM
- Parameterization, data backup and diagnostics with:
 - BOP-2 and IOP2 operator panels
 - TIA STARTDRIVE
- Setpoint channel and closed-loop control
- Control signals and signal interconnections
- Inverter functions

Practical exercises using the training device with:

SINAMICS CU240E-2 PN with PM 240 FS ASIMOTICS induction motor

The 4 day course in September will also cover

- Design and principle of operation of the SINAMICS G120 control unit and power module
- Parameterization, data backup and diagnostics with:
 - BOP-2 or IOP-2 local operator panels and TIA STARTDRIVE
 - Setpoint channel and closed-loop control modes
 - Control signals and signal interconnections
- Communication with a S7-1200 plc using a fieldbus connection (Profinet)
- Axis position control using the CU250S-2 with encoder feedback
- Drive based safety integrated

Practical exercises using the training device with:

SINAMICS CU250S-2 PN, PM 240-2, SIMOTICS induction motor and S7-1200 plc.

Prerequisites

Basic knowledge of electrical engineering.

Some prior experience using TIA-Portal, for example Siemens TIA-SERV1, TIA-PRO1 or equivalent

Note

All these learning points are reinforced with practical 'hands-on' exercises.

Type

Face-to-face training

Duration

4 days

Language

en

Fee

2,010 GBP