

## Füllstandmessung - Technologie (SC-PI2-T1E)

---

### Objectives

---

Participants will get advanced knowledge on level measurement. Covering product lines and common applications, participants learn about point and continuous level measurement, product features, product selection and troubleshooting.

### Target Group

---

- Users in the field of process instrumentation
- Sales personnel/ service personnel
- Commissioning engineers, configuring engineers

### Content

---

Combined hands-on training and theory for level measurement:

- Measurement principles
- The Siemens product portfolio SITRANS L and their technical specifications (e.g. radar, ultrasonic and static weighing)
- Handling, operation, commissioning, including remote control via SIMATIC PDM
- Diagnostics

### Prerequisites

---

- Basic knowledge of process instrumentation technology
- General knowledge of electrical engineering

### Type

---

Face-to-face training

### Duration

---

3 days

### Language

---

de