

## Prozessgaschromatograph MAXUM edition II Bedienung und Wartung (SC-C-MAX1)

---

### Short Description

---

Basics of gas chromatography

Introduction into the Process Gas Chromatograph MAXUM edition II: electronics, analytics, HMI, Gas Chromatograph Portal software structure, archiving, networking, addresses.

### Target Group

---

Service personnel

Project managers, project team members

Commissioning engineers, configuring engineers

Operators, users

### Content

---

- Introduction into chromatography
- Physical structure and electronic design of MAXUM edition II process gas chromatograph
- Analytical functions, hardware modules, electronic and analytical
- Workstation and structure of the software; devices for networking and prepare the PC
- Networking: addresses, IP, Loop, Unit Ethernet, DataNet, CAN boards
- MAXUM database: MAXUM table editor, HMI, online operation
- I/O tables, alarms, the AMD-File, backup and restore
- Operation with GCP: application, sequences, methods
- Peak tables and integration parameters
- Data sheet and nomenclature
- Valves: Model 50 and liquid injection valve
- Applets and use of detectors
- Column switching, electronic pressure regulators and flow adjustment
- Development of a method

### Prerequisites

---

Basic knowledge in process analytics

### Type

---

Face-to-face training

### Duration

---

4.5 days

### Language

---

de