



SINAMICS G120 Commissioning and Service Advanced Course / SINAMICS G120服务与调试高级课程 (D7227)

Objectives

This course will teach you about drive-based safety functions and communication via PROFINET. You will learn how to use the basic positioner functions of the CU250-2 Control Unit for single-axis motion control applications

Target Group

Programmer and Commissioning engineers

Content

- Commissioning the SINAMICS G120 in the TIA Portal with Startdrive
- Basic positioned:
 - Commissioning and closed-loop position control
 - Operating modes and traversing blocks
- Communication with SIMATIC S7 via PROFINET
- Control modes and measuring functions
- Technology controller: Commissioning and adaptation
- Drive-based safety functions via terminals
- Interconnection of signals with free function blocks.
- Practical exercises on training cases(G120)

Prerequisites

Basic knowledge of D7210 and TIA Portal

Type

Face-to-face training

Duration

3 days

Language

en, zh

Fee

4,000 CNY