

Online training Wireless LAN in Industrial Networks with SCALANCE W products (IK-IWLANS)

Objectives

In industrial environments, WLAN is exposed to more extreme conditions, such as temperature fluctuations, humidity, dust, etc. In addition, a high-degree of reliability and performance is expected from these systems. At the same time, these industrial WLAN networks (IWLAN for short) provide a great deal of flexibility for companies in the implementation of complex applications indoors and outdoors. Thus, with Safety Integrated, applications can also be wirelessly implemented and seamlessly connected to Industrial Ethernet with PROFINET components.

The course teaches the configuration, planning, and operation of IWLAN, also in interaction with real-time-capable systems. To ensure that the theoretical knowledge can later be implemented, we value in-depth practical exercises during the training. You can deepen your theoretical knowledge with numerous practical exercises on products from the SCALANCE W product line.

At the end of the course, you will know the requirements for wireless solutions in industrial networks. You will learn the fundamentals and knowledge required to plan, implement and support for plain mobile networks.

Target Group

Decision makers
Planners
Sales personnel
Configuring engineers
Commissioning engineers
Engineering personnel
Project engineers
Maintenance personnel
Service personnel
Industry: COOs
IT: CIOs, network planners and administrators

Content

Comparison and coexistence of different wireless technologies
Theoretical fundamentals of wireless technology
Security and high data rates in WLAN
Introduction to the different WLAN standards
Planning and configuration of different radio links
Planning and configuration of RCOAX radio networks with iPCF
Planning and configuration of free radio networks with iPCF-MC
Comprehensive exercises using the SCALANCE W product line

Prerequisites

- Knowledge according to the course "[Ethernet Fundamentals in Industrial Networks](#)" (IK-ETHBAS)
- You should have basic knowledge of the topic "Ethernet" and should be familiar with topologies, transfer processes, addressing, data transport and understand the associated technical vocabulary. It is also helpful if you are familiar with the principles of operation of routers, switches, hubs and the OSI reference model.
- Basic knowledge of SIMATIC S7 and knowledge from the courses "[Simatic S7 programming 2](#)" (ST-PRO2) or "[Simatic S7 service 2](#)" (ST-SERV2); courses is desirable.

Note

Certification (Siemens CPIN-LEVEL)

After the training course, you have the opportunity to become certified as "Siemens Certified Professional for Industrial Networks - Wireless LAN". The certification examination takes place at the end of this training. As an option, the examination may be taken at a later time.

For further information, read here

<https://www.sitrain-learning.siemens.com/SE/sv/content/Certifieringsprogram-inom-Industrial-Networks.do>

Please note that before the examination you have to identify yourself by showing a valid photo identification.

Type

Online-Training

Duration

3 days

Language

en

Fee

19,500 SEK

copyright by Siemens AG 2026