

Please scroll down for English version

中文版:



西门子工业技术培训中心新闻

SITRAIN简介

**SITRAIN** 是西门子工业技术的官方培训机构，是西门子工业技术培训的理念。它不仅代表着培训课程、远程教学，还代表着更完整、更广泛的售后服务与支持。**SITRAIN**在全球**60**多个国家拥有**200**多家专业的西门子工业技术培训中心，提供全球统一的培训课程。**27**年来，我们为中国本地的工业客户提供专业的课程和人才发展服务。  
新年伊始，西门子工业技术培训中心祝大家**2018**年幸福健康，事业顺利！

足不出户，体验西门子网络课程

西门子在中国首次推出西门子工业网络专家培训认证体系

近期课程安排（点击课程名称可查看详细培训内容）

- 工业4.0系列课程
- TIA Portal（TIA 博途）系列课程
- SIMATIC S7-200/300/400 可编程控制器
- SIMATIC 工业通讯网络
- SIMATIC 人机界面
- SIMATIC PCS7 过程控制系统
- 低压传动装置
- 中压传动装置
- 数控系统
- SIMOTION 运动控制系统
- 过程仪表、称重系统、分析仪表
- 楼宇控制
- 低压配电、电机控制与保护产品

■ 足不出户，体验西门子网络课程

**WBT-Web Based Training**作为全新的数字化学习模式可以帮助学员随时随地的学习最新工业技术，**SITRAIN**为您准备的以下六门基础课程，以多媒体交互的方式让您更灵活，更准确，更高效的掌握从**PLC**、网络、过程控制到驱动及变频原理的丰富知识，我们将以更加灵活高效的学习方式带您走进数字化学习时代。  
点课程代号或课程名称了解更多课程信息：

| 课程代号                  | 课程名称                                  | 天数   | 价格<br>(含6%增值税) |
|-----------------------|---------------------------------------|------|----------------|
| <a href="#">W1201</a> | <a href="#">交流电机基础</a>                | 6 小时 | 300            |
| <a href="#">W1202</a> | <a href="#">交流变频器基础</a>               | 6 小时 | 300            |
| <a href="#">W1101</a> | <a href="#">PLC基础</a>                 | 6 小时 | 200            |
| <a href="#">W1102</a> | <a href="#">过程自动化中的PROFIBUS现场总线基础</a> | 6 小时 | 200            |
| <a href="#">W1103</a> | <a href="#">PROFINET基础</a>            | 6 小时 | 200            |
| <a href="#">W1104</a> | <a href="#">过程控制工程入门</a>              | 6 小时 | 200            |

■ 西门子在中国首次推出西门子工业网络专家培训认证体系

随着工业物联网、工业大数据、人工智能等技术的蓬勃发展，传统工业企业为了提高自身竞争力纷纷期望迅速能够转型为数字化企业。西门子也提出了“从电气化、自动化到数字化”的公司战略，基于西门子数字化企业平台，为用户提供从产品生命周期、设备生命周期到整个制造运营生命周期三大维度的工业**4.0**实现路径，从而帮助用户满足快速产品交付、个性化制造和高效生产的全新生产需求。而企业要实现数字化，在其工业领域就必须拥有一个强大的工业通讯网络来实现高效、可靠、安全、实时的数据传输来实现价值链的垂直集成和水平集成。

构建满足工业**4.0**和智能制造要求的强大工业通讯网络需要专业合格的工业网络技术人才，因此西门子适时推出了基于工业以太网国际标准的培训认证体系。在**2018**年，西门涵盖了从工业以太网基础，到高级交换和路由技术、工业网络安全技术和工业无线网络技术的培训认证课程将陆续在**SITRAIN**设在北京、上海和广州的培训中心开展。具体的认证课程信息及时间请参见[西门子培训网站](#)。

■ 近期课程安排（点击课程名称可查看详细培训内容）

工业**4.0**系列课程

| 课程代号                     | 课程名称                              | 开课时间  | 城市 | 价格<br>(含6%增值税) |
|--------------------------|-----------------------------------|-------|----|----------------|
| <a href="#">F4002</a>    | <a href="#">基于全新TIA博途的数字化解决方案</a> | 05.14 | 北京 | 7500           |
| <a href="#">F4003（新）</a> | <a href="#">从规划到实施：一个鼠标的数字化之旅</a> | 04.24 | 上海 | 3600           |

TIA Portal（TIA 博途）系列课程

| 课程代号                       | 课程名称                                                    | 开课时间  | 城市    | 价格<br>(含6%增值税) |
|----------------------------|---------------------------------------------------------|-------|-------|----------------|
| <a href="#">A7811</a>      | <a href="#">SIMATIC S7-1500 系统、维护与编程综合课程（基于 TIA 博途）</a> | 04.09 | 武汉    | 12000          |
|                            |                                                         | 04.16 | 沈阳    |                |
|                            |                                                         | 05.07 | 北京/上海 |                |
|                            |                                                         | 05.14 | 沈阳/重庆 |                |
| <a href="#">A7811CP（新）</a> | <a href="#">西门子自动化维护工程师基础认证考试（基于 TIA 博途）</a>            | 05.21 | 广州    | 1000           |
|                            |                                                         | 03.24 | 重庆    |                |
|                            |                                                         | 04.21 | 上海/武汉 |                |
|                            |                                                         | 05.28 | 沈阳    |                |
| <a href="#">A7811CP（新）</a> | <a href="#">西门子自动化维护工程师基础认证考试（基于 TIA 博途）</a>            | 03.26 | 沈阳    | 1000           |
|                            |                                                         | 03.26 | 沈阳    |                |

2018.03



热点链接

关于我们

- 培训中心
- 培训销售经理
- 培训须知

报名工具箱

- 课程查询及在线预订
- 培训手册（2018）
- 课程计划（2018）
- 课程注册表

培训中心网站

[www.siemens.com.cn/sitrain](#)

课程咨询热线

4008104288 -4

培训中心联系方式

北京： 010-64768958  
上海： 021-62815933  
广州： 020-37182012  
沈阳： 024-82518220  
武汉： 027-85486688-6400  
重庆： 023-63818887

|                            |                                                               |       |       |       |
|----------------------------|---------------------------------------------------------------|-------|-------|-------|
| <a href="#">A7812</a>      | <a href="#">SIMATIC S7-1500 高级维护课程（基于 TIA 博途）</a>             | 04.09 | 北京    |       |
|                            |                                                               | 05.21 | 上海    | 6500  |
| <a href="#">A7812CP（新）</a> | <a href="#">西门子自动化维护工程师认证考试（基于 TIA 博途）</a>                    | 04.14 | 北京    | 1200  |
|                            |                                                               | 05.26 | 上海    |       |
| <a href="#">A7813</a>      | <a href="#">SIMATIC S7-1500 高级编程课程（基于 TIA 博途）</a>             | 03.26 | 广州    | 10000 |
|                            |                                                               | 05.30 | 沈阳    |       |
| <a href="#">A7813CP（新）</a> | <a href="#">西门子S7系统开发工程师认证考试（基于 TIA 博途）</a>                   | 03.29 | 北京    | 1200  |
| <a href="#">A7821</a>      | <a href="#">SIMATIC S7-SCL结构化控制语言编程（基于 TIA 博途）</a>            | 03.19 | 上海    | 3900  |
|                            |                                                               | 04.02 | 北京    |       |
| <a href="#">A7822</a>      | <a href="#">SIMATIC S7-GRAPH 顺序控制编程（基于 TIA 博途）</a>            | 03.22 | 上海    | 2600  |
|                            |                                                               | 03.29 | 北京    |       |
| <a href="#">A7823</a>      | <a href="#">SIMATIC S7-1500 分布式安全系统的调试与编程（基于 TIA 博途）</a>      | 04.02 | 北京    | 3900  |
|                            |                                                               | 05.02 | 上海    |       |
| <a href="#">A7824（新）</a>   | <a href="#">SIMATIC S7-1500/1500T 运动控制系统调试课程（基于 TIA 博途）</a>   | 04.09 | 北京    | 6500  |
| <a href="#">A7831</a>      | <a href="#">PROFINET/工业以太网系统课程（基于 TIA 博途）</a>                 | 05.21 | 北京    | 6500  |
|                            |                                                               | 04.09 | 广州    |       |
| <a href="#">A7816</a>      | <a href="#">SIMATIC S7-1500 与TIA Portal（基于 TIA 博途）升级课程</a>    | 04.16 | 重庆    | 6500  |
|                            |                                                               | 05.28 | 北京/上海 |       |
| <a href="#">A7815</a>      | <a href="#">SIMATIC S7-300/400 与TIA Portal（基于 TIA 博途）升级课程</a> | 04.23 | 上海    | 6500  |
|                            |                                                               | 04.09 | 北京    |       |
| <a href="#">A7852</a>      | <a href="#">SIMATIC WinCC 操作员面板系统课程（基于 TIA 博途）</a>            | 04.10 | 沈阳    | 5200  |
|                            |                                                               | 04.23 | 武汉    |       |
|                            |                                                               | 05.07 | 重庆    |       |
| <a href="#">A7115</a>      | <a href="#">SIMATIC S7-1200 系统课程（基于 TIA 博途）</a>               | 03.26 | 上海    | 6500  |
|                            |                                                               | 04.16 | 广州    |       |

#### SIMATIC S7-200/300/400 可编程控制器

| 课程代号                    | 课程名称                                                          | 开课时间  | 城市              | 价格<br>(含6%增值税) |
|-------------------------|---------------------------------------------------------------|-------|-----------------|----------------|
|                         |                                                               | 03.12 | 沈阳              |                |
|                         |                                                               | 04.09 | 上海/沈阳/重庆        |                |
| <a href="#">A7111</a>   | <a href="#">SIMATIC S7-300/400 系统、维护与编程综合课程（基于STEP7 V5.x）</a> | 04.16 | 北京/广州           | 11200          |
|                         |                                                               | 05.07 | 北京/沈阳/<br>武汉/重庆 |                |
|                         |                                                               | 05.28 | 上海              |                |
|                         |                                                               | 03.17 | 上海/重庆           |                |
| <a href="#">A7111CP</a> | <a href="#">西门子自动化维护工程师基础认证考试</a>                             | 04.28 | 广州              | 900            |
|                         |                                                               | 05.19 | 北京/武汉           |                |
|                         |                                                               | 03.19 | 广州/重庆           |                |
| <a href="#">A7112</a>   | <a href="#">SIMATIC S7 高级维护课程（基于STEP7 V5.x）</a>               | 03.26 | 沈阳              | 8200           |
|                         |                                                               | 05.03 | 上海              |                |
|                         |                                                               | 05.21 | 北京/武汉           |                |
|                         |                                                               | 03.28 | 重庆              |                |
| <a href="#">A7112CP</a> | <a href="#">西门子自动化维护工程师认证考试</a>                               | 04.04 | 沈阳              | 1100           |
|                         |                                                               | 05.12 | 上海              |                |
|                         |                                                               | 05.30 | 武汉              |                |
|                         |                                                               | 03.19 | 北京              |                |
|                         |                                                               | 03.26 | 武汉              |                |
| <a href="#">A7113</a>   | <a href="#">SIMATIC S7 高级编程课程（基于STEP7 V5.x）</a>               | 04.16 | 沈阳/重庆           | 9300           |
|                         |                                                               | 05.02 | 广州              |                |
|                         |                                                               | 05.14 | 上海              |                |
|                         |                                                               | 03.09 | 北京              |                |
| <a href="#">A7113CP</a> | <a href="#">西门子S7系统开发工程师认证考试</a>                              | 04.26 | 沈阳/重庆           | 1100           |
|                         |                                                               | 05.12 | 广州              |                |
|                         |                                                               | 05.24 | 上海              |                |
|                         |                                                               | 04.02 | 北京              |                |
| <a href="#">A7122</a>   | <a href="#">SIMATIC S7 分布式安全系统的调试与编程（基于STEP7 V5.x）</a>        | 05.02 | 上海              | 3900           |
|                         |                                                               | 05.15 | 广州              |                |
|                         |                                                               | 05.21 | 重庆              |                |
|                         |                                                               | 04.08 | 广州              |                |
| <a href="#">A1474</a>   | <a href="#">SIMATIC S7-GRAPH 顺序控制编程</a>                       | 04.23 | 上海              | 3750           |
|                         |                                                               | 05.02 | 北京              |                |
| <a href="#">A1476</a>   | <a href="#">SIMATIC S7-CFC 连续功能图编程</a>                        | 04.09 | 北京              | 2500           |

|                       |                                                             |       |       |      |
|-----------------------|-------------------------------------------------------------|-------|-------|------|
| <a href="#">A1480</a> | <a href="#">SIMATIC S7-SCL 结构化控制语言编程</a>                    | 04.11 | 北京/广州 | 2500 |
| <a href="#">A7415</a> | <a href="#">基于PDIAG和ProAgent的过程诊断</a>                       | 05.03 | 武汉    | 2500 |
| <a href="#">A7412</a> | <a href="#">基于SIMATIC S7的PID理论与应用课程</a>                     | 05.02 | 北京    | 3900 |
| <a href="#">A7411</a> | <a href="#">控制系统的抗干扰分析与Profibus诊断</a>                       | 05.03 | 北京    | 3200 |
| <a href="#">A7414</a> | <a href="#">西门子无线射频识别系统（RFID）</a>                           | 05.30 | 武汉    | 2600 |
| <a href="#">A1172</a> | <a href="#">基于SIMATIC S7-200/200 CN/200 SMART的小型自动化系统课程</a> | 03.26 | 上海    | 4500 |

#### SIMATIC 工业通讯网络

| 课程代号                  | 课程名称                                         | 开课时间  | 城市       | 价格<br>(含6%增值税) |
|-----------------------|----------------------------------------------|-------|----------|----------------|
|                       |                                              | 03.12 | 北京       |                |
|                       |                                              | 03.19 | 武汉/重庆    |                |
| <a href="#">A7225</a> | <a href="#">PROFINET/工业以太网系统课程</a>           | 04.23 | 上海       | 5800           |
|                       |                                              | 05.21 | 广州       |                |
|                       |                                              | 05.28 | 武汉       |                |
| <a href="#">A7226</a> | <a href="#">工业无线射频（IWLAN）系统课程</a>            | 05.30 | 上海       | 2600           |
|                       |                                              | 04.23 | 沈阳/武汉/重庆 |                |
| <a href="#">A1497</a> | <a href="#">PROFIBUS现场总线的网络调试、维护及现场设备的集成</a> | 05.14 | 北京       | 5800           |
|                       |                                              | 05.28 | 广州       |                |

#### SIMATIC 人机界面

| 课程代号                  | 课程名称                                     | 开课时间  | 城市       | 价格<br>(含6%增值税) |
|-----------------------|------------------------------------------|-------|----------|----------------|
| <a href="#">A1479</a> | <a href="#">WinCC 系统课程</a>               | 05.03 | 北京/上海/广州 | 7800           |
|                       |                                          | 05.21 | 沈阳       |                |
|                       |                                          | 04.16 | 上海       |                |
| <a href="#">A1484</a> | <a href="#">WinCC Flexible 操作员面板系统课程</a> | 04.23 | 北京       | 5500           |
|                       |                                          | 05.07 | 重庆       |                |
|                       |                                          | 05.14 | 广州       |                |

#### SIMATIC PCS7 过程控制系统

| 课程代号                    | 课程名称                                           | 开课时间  | 城市    | 价格<br>(含6%增值税) |
|-------------------------|------------------------------------------------|-------|-------|----------------|
|                         |                                                | 03.12 | 上海/武汉 |                |
| <a href="#">A1501</a>   | <a href="#">SIMATIC PCS7 系统课程</a>              | 04.09 | 武汉    | 11500          |
|                         |                                                | 05.14 | 上海    |                |
|                         |                                                | 05.21 | 北京    |                |
| <a href="#">A1501CP</a> | <a href="#">西门子PCS7 基础工程师认证考试</a>              | 05.25 | 上海    | 600            |
|                         |                                                | 03.19 | 北京    |                |
| <a href="#">A1503</a>   | <a href="#">SIMATIC PCS7 高级系统课程</a>            | 04.09 | 上海    | 12500          |
|                         |                                                | 03.31 | 北京    |                |
| <a href="#">A1503CP</a> | <a href="#">西门子PCS7 系统工程师认证考试</a>              | 04.20 | 上海    | 1100           |
| <a href="#">A7121</a>   | <a href="#">SIMATIC PCS7 过程安全系统(SIS)的测试与编程</a> | 04.02 | 上海    | 4000           |

#### 低压传动装置

| 课程代号                  | 课程名称                                               | 开课时间  | 城市    | 价格<br>(含6%增值税) |
|-----------------------|----------------------------------------------------|-------|-------|----------------|
| <a href="#">D7400</a> | <a href="#">驱动技术原理</a>                             | 03.19 | 北京    | 5100           |
|                       |                                                    | 03.26 | 北京    |                |
| <a href="#">D7212</a> | <a href="#">SINAMICS S120 服务与调试课程(伺服控制)</a>        | 05.07 | 北京    | 6200           |
|                       |                                                    | 05.28 | 上海/沈阳 |                |
| <a href="#">D7226</a> | <a href="#">SINAMICS S120 服务与调试高级课程(伺服控制)</a>      | 03.26 | 上海    | 6200           |
|                       |                                                    | 05.14 | 北京    |                |
| <a href="#">D7213</a> | <a href="#">SINAMICS S120 CM 驱动模块服务与调试课程(矢量控制)</a> | 03.12 | 北京    | 6200           |
|                       |                                                    | 05.07 | 武汉    |                |
| <a href="#">D7219</a> | <a href="#">SINAMICS S120 诊断与维护课程</a>              | 03.12 | 上海/广州 | 6200           |
|                       |                                                    | 05.07 | 上海    |                |
| <a href="#">D7224</a> | <a href="#">SINAMICS 维修课程</a>                      | 04.09 | 北京    | 6800           |
| <a href="#">D7223</a> | <a href="#">SINAMICS S120 驱动安全集成</a>               | 04.10 | 上海    | 5000           |
|                       |                                                    | 05.21 | 北京    |                |
| <a href="#">D7218</a> | <a href="#">SINAMICS S120 系统配置与选型(SIZER)</a>       | 04.02 | 上海    | 3900           |
|                       |                                                    | 05.28 | 北京    |                |
| <a href="#">D7211</a> | <a href="#">SINAMICS G150/G130/S150服务与调试课程</a>     | 04.16 | 北京    | 6200           |
|                       |                                                    | 05.21 | 广州    |                |

|                           |                                                   |       |    |      |
|---------------------------|---------------------------------------------------|-------|----|------|
| <a href="#">D7210</a>     | <a href="#">SINAMICS G120 服务与调试课程</a>             | 04.02 | 北京 |      |
|                           |                                                   | 04.23 | 上海 | 3600 |
| <a href="#">D7227 (新)</a> | <a href="#">SINAMICS G120 服务与调试高级课程</a>           | 04.26 | 上海 | 3600 |
|                           |                                                   | 04.16 | 上海 |      |
| <a href="#">D7111</a>     | <a href="#">SINAMICS DCM (6RA80)直流传动装置服务与调试课程</a> | 04.23 | 北京 | 6200 |
| <a href="#">D2104</a>     | <a href="#">6SE70变频器维修维护课程</a>                    | 05.07 | 北京 | 6200 |
| <a href="#">E2101</a>     | <a href="#">驱动系统电磁兼容 (EMC) 课程</a>                 | 04.02 | 北京 | 3200 |

#### 中压传动装置

| 课程代号                  | 课程名称                                   | 开课时间 | 城市   | 价格<br>(含6%增值税) |
|-----------------------|----------------------------------------|------|------|----------------|
| <a href="#">D7216</a> | <a href="#">PH 完美无谐波GH180系列变频器服务课程</a> | 3.28 | SEDS | 5000           |
|                       |                                        | 5.09 |      |                |

#### 数控系统

| 课程代号                  | 课程名称                                             | 开课时间  | 城市 | 价格<br>(含6%增值税) |
|-----------------------|--------------------------------------------------|-------|----|----------------|
|                       |                                                  | 03.12 | 上海 |                |
|                       |                                                  | 05.14 |    |                |
| <a href="#">T8401</a> | <a href="#">SINUMERIK 840D SL 维修与调整</a>          | 04.09 | 北京 | 11500          |
|                       |                                                  | 05.07 |    |                |
| <a href="#">T8402</a> | <a href="#">SINUMERIK 840D SL / 840D PLC基础应用</a> | 04.23 | 北京 | 5600           |
| <a href="#">T8403</a> | <a href="#">SINUMERIK 840D SL 安全集成的组态与调试</a>     | 03.26 | 北京 | 6800           |
|                       |                                                  | 04.09 | 上海 |                |
| <a href="#">T8404</a> | <a href="#">SINUMERIK 840D SL 刀具管理基础</a>         | 03.19 | 北京 | 6400           |
|                       |                                                  | 04.23 | 北京 |                |
| <a href="#">A2485</a> | <a href="#">SINUMERIK 840D 维修与调整高级课程</a>         | 05.28 | 上海 | 6800           |
|                       |                                                  | 03.26 | 上海 |                |
| <a href="#">T8281</a> | <a href="#">SINUMERIK 828D 维修与调整</a>             | 04.09 | 北京 | 10400          |
|                       |                                                  | 03.19 | 北京 |                |
| <a href="#">T8282</a> | <a href="#">SINUMERIK Operate 操作与编程</a>          | 04.16 | 上海 | 6000           |
|                       |                                                  | 05.21 | 北京 |                |
| <a href="#">A2482</a> | <a href="#">SINUMERIK HMI Advanced 操作与编程</a>     | 05.21 | 北京 | 6000           |
| <a href="#">A2489</a> | <a href="#">SINUMERIK 840D SL/ 840D NC高级编程</a>   | 05.28 | 北京 | 6800           |
| <a href="#">A2400</a> | <a href="#">数控基础课程</a>                           | 03.26 | 北京 | 5600           |

#### SIMOTION 运动控制系统

| 课程代号                  | 课程名称                                | 开课时间  | 城市    | 价格<br>(含6%增值税) |
|-----------------------|-------------------------------------|-------|-------|----------------|
|                       |                                     | 03.26 | 北京    |                |
| <a href="#">A3101</a> | <a href="#">SIMOTION 运动控制系统基础课程</a> | 05.07 | 北京    | 6500           |
|                       |                                     | 05.14 | 上海    |                |
| <a href="#">A3102</a> | <a href="#">SIMOTION 运动控制系统编程课程</a> | 05.14 | 北京    | 6500           |
| <a href="#">A3108</a> | <a href="#">SIMOTION 运动控制系统维护课程</a> | 05.21 | 北京/上海 | 6500           |

#### 过程仪表、称重系统、分析仪表

| 课程代号                  | 课程名称                                                            | 开课时间  | 城市 | 价格<br>(含6%增值税) |
|-----------------------|-----------------------------------------------------------------|-------|----|----------------|
| <a href="#">P1101</a> | <a href="#">SITRANS P 压力仪表、SITRANS T 温度仪表及 SIPART 阀门定位器技术培训</a> | 04.09 | 大连 | 5100           |
| <a href="#">P1102</a> | <a href="#">SITRANS F 流量仪表技术培训</a>                              | 04.16 | 大连 | 5100           |
| <a href="#">P1103</a> | <a href="#">SITRANS L 物位仪表技术培训</a>                              | 04.23 | 大连 | 5100           |
| <a href="#">P1104</a> | <a href="#">Siwarex 集成化静态称重产品培训</a>                             | 03.26 | 大连 | 2600           |
| <a href="#">P1105</a> | <a href="#">动态称重产品培训</a>                                        | 03.08 | 大连 | 3800           |
|                       |                                                                 | 04.16 | 大连 |                |
| <a href="#">P2101</a> | <a href="#">Maxum II 气相色谱仪</a>                                  | 05.21 | 大连 | 9000           |

#### 楼宇控制

| 课程代号                  | 课程名称                                     | 开课时间  | 城市 | 价格<br>(含6%增值税) |
|-----------------------|------------------------------------------|-------|----|----------------|
| <a href="#">E1002</a> | <a href="#">KNX 智能家居与楼宇控制高级应用课程</a>      | 03.12 | 上海 | 5250           |
| <a href="#">E1006</a> | <a href="#">APOGEE 顶峰楼宇控制系统编程与调试综合课程</a> | 04.16 | 广州 | 5300           |

#### 低压配电、电机控制与保护产品

| 课程代号                  | 课程名称                                         | 开课时间  | 城市 | 价格<br>(含6%增值税) |
|-----------------------|----------------------------------------------|-------|----|----------------|
| <a href="#">D3101</a> | <a href="#">SIMOCODE Pro 电机控制与监视装置的编程与调试</a> | 03.19 | 北京 | 2200           |
|                       |                                              | 03.21 | 北京 |                |
| <a href="#">D3103</a> | <a href="#">低压配电和配电监控系统</a>                  | 04.02 | 上海 | 3400           |

更多详细信息，请关注培训官方网站

➤ [www.siemens.com.cn/sitrain](http://www.siemens.com.cn/sitrain)

培训，助力个人卓越，成就企业发展！

English Version:



## News of Siemens Industry Technical Training Center

2018.03

**SITRAIN** is the Siemens industry technical training institution. It also is the idea of the Siemens industrial technical training. It not only represents the training course, remote teaching, also represents more complete, more extensive after-sales service and support. SITRAIN has over 200 professional Siemens industrial technology training centers, providing global unified training courses in 60 countries. We provide for Chinese local professional courses and talent development services for 27 years. In this festive season, we wish you a healthy, successful and happiness 2018!



Hot Link

About Us

- Training Center
- Regional Training Consultant
- Terms and Conditions

Training Information

- Course queries and online booking
- Course Handbook(2018)
- Course Plan(2018)
- Course Application eForm

Training Center Web Site

➤ <http://www.siemens.com.cn/sitrain>

Course Hotline

4008104288 -4

Training Center Contact Information

Beijing: 010-64768958  
Shanghai: 021-62815933  
Guangzhou: 020-37182012  
Shenyang: 024-82518220  
Wuhan: 027-85486688-6400  
Chongqing: 023-63818887

**Web-Based Training is coming!**

**SIEMENS launch a Siemens certification training courses for Industrial Networks in China**

**Training Plan(Click on the course name for more information)**

- Industry 4.0 Solution Series Course
- TIA Portal Series
- SIMATIC S7-200/300/400
- SIMATIC NET
- SIMATIC HMI
- SIMATIC PCS7
- Low Voltage Drive Device
- Medium Voltage Drive Device
- SINUMERIK CNC Control
- SIMOTION Motion Control
- Process Instrumentation & Sensor
- Building Control
- Low-Voltage Power Distribution, Control and Protection

■ **Web-Based Training is coming!**

Web-Based Training as a new digital learning method that can help students to learn up-to-date industrial technology in anytime and anywhere, SITRAIN offered six basic WBT courses as below, guide you to be more flexible, more accurate and more efficient through interactive environment to study the basic of PLC, PROFINET, Process Control System and Drive knowledge, we try to find best flexible and efficient way to lead students run into the era of digital learning.

| Course ID             | Course Name                                                 | Date    | Price ( CNY ) |
|-----------------------|-------------------------------------------------------------|---------|---------------|
| <a href="#">W1201</a> | <a href="#">Basics of Drive Technology – AC Motors</a>      | 6 hours | 300           |
| <a href="#">W1202</a> | <a href="#">Basics of Drive Technology – AC Converters</a>  | 6 hours | 300           |
| <a href="#">W1101</a> | <a href="#">PLCs for Beginners</a>                          | 6 hours | 200           |
| <a href="#">W1102</a> | <a href="#">PROFIBUS in Process Automation – the Basics</a> | 6 hours | 200           |
| <a href="#">W1103</a> | <a href="#">PROFINET</a>                                    | 6 hours | 200           |
| <a href="#">W1104</a> | <a href="#">Process Control Engineering for Beginner</a>    | 6 hours | 200           |

■ **SIEMENS launch a Siemens certification training courses for Industrial Networks in China**

In recent years, new technologies like Industrial Internet of things (IIoT), Big Data, Artificial Intelligence(AI), etc. have been developed tremendously, and in order to improve market competence, many traditional industrial enterprises are desperate for evolving to digital enterprises. Siemens also announced its corporate strategy which is "from electrification, automation to digitalization". Based on a digitalized enterprise platform, Siemens offers its customers a clear path consisting of three dimensions covering product life cycle, device life cycle management and the entire manufacturing and operation life cycle. With the help of this platform, it is possible for customers to fulfill the most critical needs such as fast product delivery, customized mass manufacturing and efficient production. But to realize digitalization, a strong industrial communication network that is highly efficient, highly reliable, highly secure and real-time is always the foundation for the vertical and horizontal integration of the entire value chain.

One of the key elements out of Industry 4.0 and Intelligent Manufacturing of every enterprise is to make sure that they have the capable and professional industrial networking experts in place. Siemens, with its global certification training courses of Industrial Networking, enable and guarantee such capability and expertise. In 2018, four industrial network certification courses covering basics of Industrial Networks, advanced switching and routing technology, Industrial Security Technology and Industrial Wireless Technology will be opened for training registration and these 4 courses will be held in training centers of SITRAIN located in Beijing, Shanghai de Guangzhou. ➤ [More details please refer to SITRAIN website.](#)

■ **Training Plan(Click on the course name for more information)**

**Industry 4.0 Solution Series Course**

| Course ID                  | Course Name                                                                           | Date  | City     | Price ( CNY ) |
|----------------------------|---------------------------------------------------------------------------------------|-------|----------|---------------|
| <a href="#">F4002</a>      | <a href="#">Digitalization Solution based on TIA Portal</a>                           | 05.14 | Beijing  | 7500          |
| <a href="#">F4003(new)</a> | <a href="#">From Planning to Execution:The digitalization excursion of a PC mouse</a> | 04.24 | Shanghai | 3600          |

**TIA Portal Series**

| Course ID | Course Name | Date | City | Price ( CNY ) |
|-----------|-------------|------|------|---------------|
|-----------|-------------|------|------|---------------|

|                              |                                                                                                     |       |                    |       |
|------------------------------|-----------------------------------------------------------------------------------------------------|-------|--------------------|-------|
|                              |                                                                                                     | 04.09 | Wuhan              |       |
|                              |                                                                                                     | 04.16 | Shenyang           |       |
| <a href="#">A7811</a>        | <a href="#">SIMATIC S7-1500 System, Service &amp; Programming Plus Course (based on TIA Portal)</a> | 05.07 | Beijing/Shanghai   | 12000 |
|                              |                                                                                                     | 05.14 | Shenyang/Chongqing |       |
|                              |                                                                                                     | 05.21 | Guangzhou          |       |
|                              |                                                                                                     | 03.24 | Chongqing          |       |
| <a href="#">A7811CP(new)</a> | <a href="#">Test: Siemens Certified Service Technician Level 1 in the TIA Portal</a>                | 04.21 | Shanghai/Wuhan     | 1000  |
|                              |                                                                                                     | 05.28 | Shenyang           |       |
|                              |                                                                                                     | 03.26 | Shenyang           |       |
| <a href="#">A7812</a>        | <a href="#">SIMATIC S7-1500 Advanced Service Course (based on TIA Portal)</a>                       | 04.09 | Beijing            | 6500  |
|                              |                                                                                                     | 05.21 | Shanghai           |       |
| <a href="#">A7812CP(new)</a> | <a href="#">Test: Siemens Certified Service Technician Level 2 in the TIA Portal</a>                | 04.14 | Beijing            | 1200  |
|                              |                                                                                                     | 05.26 | Shanghai           |       |
| <a href="#">A7813</a>        | <a href="#">SIMATIC S7-1500 Advanced Programming Course (based on TIA Portal)</a>                   | 03.26 | Guangzhou          | 10000 |
|                              |                                                                                                     | 05.30 | Shenyang           |       |
| <a href="#">A7813CP(new)</a> | <a href="#">Test: Siemens Certified S7 Programmer in the TIA Portal</a>                             | 03.29 | Beijing            | 1200  |
|                              |                                                                                                     | 03.19 | Shanghai           |       |
| <a href="#">A7821</a>        | <a href="#">SIMATIC S7, Programming with SCL based on TIA Portal</a>                                | 04.02 | Beijing            | 3900  |
|                              |                                                                                                     | 03.22 | Shanghai           |       |
| <a href="#">A7822</a>        | <a href="#">SIMATIC S7, Programming with S7-GRAH based on TIA Portal</a>                            | 03.29 | Beijing            | 2600  |
|                              |                                                                                                     | 04.02 | Beijing            |       |
| <a href="#">A7823</a>        | <a href="#">Design and Programming of SIMATIC S7-1500F Distributed Safety (based on TIA Portal)</a> | 05.02 | Shanghai           | 3900  |
| <a href="#">A7824(new)</a>   | <a href="#">SIMATIC S7-1500/1500T Motion Control in the TIA Portal</a>                              | 04.09 | Beijing            | 6500  |
| <a href="#">A7831</a>        | <a href="#">PROFINET with Industrial Ethernet in the TIA Portal</a>                                 | 05.21 | Beijing            | 6500  |
|                              |                                                                                                     | 04.09 | Guangzhou          |       |
| <a href="#">A7816</a>        | <a href="#">SIMATIC TIA Portal System Retraining Course for SIMATIC S7-1500</a>                     | 04.16 | Chongqing          | 6500  |
|                              |                                                                                                     | 05.28 | Beijing/Shanghai   |       |
| <a href="#">A7815</a>        | <a href="#">SIMATIC TIA Portal System Retraining Course for SIMATIC S7-300/400</a>                  | 04.23 | Shanghai           | 6500  |
|                              |                                                                                                     | 04.09 | Beijing            |       |
|                              |                                                                                                     | 04.10 | Shenyang           |       |
| <a href="#">A7852</a>        | <a href="#">SIMATIC TIA Portal WinCC on the machine level</a>                                       | 04.23 | Wuhan              | 5200  |
|                              |                                                                                                     | 05.07 | Chongqing          |       |
|                              |                                                                                                     | 03.26 | Shanghai           |       |
| <a href="#">A7115</a>        | <a href="#">SIMATIC S7-1200 System Course (based on TIA Portal)</a>                                 | 04.16 | Guangzhou          | 6500  |

#### SIMATIC S7-200/300/400

| Course ID               | Course Name                                                                                            | Date  | City                             | Price ( CNY ) |
|-------------------------|--------------------------------------------------------------------------------------------------------|-------|----------------------------------|---------------|
| <a href="#">A7111</a>   | <a href="#">SIMATIC S7-300/400 System, Service &amp; Programming Plus Course (based on STEP7 V5.x)</a> | 03.12 | Shenyang                         |               |
|                         |                                                                                                        | 04.09 | Shanghai/Shenyang/Chongqing      |               |
|                         |                                                                                                        | 04.16 | Beijing/Guangzhou                | 11200         |
|                         |                                                                                                        | 05.07 | Beijing/Shenyang/Wuhan/Chongqing |               |
|                         |                                                                                                        | 05.28 | Shanghai                         |               |
| <a href="#">A7111CP</a> | <a href="#">Test: Siemens Certified Service Technician Level 1</a>                                     | 03.17 | Shanghai/Chongqing               |               |
|                         |                                                                                                        | 04.28 | Guangzhou                        | 900           |
|                         |                                                                                                        | 05.19 | Beijing/Wuhan                    |               |
|                         |                                                                                                        | 03.19 | Guangzhou/Chongqing              |               |
| <a href="#">A7112</a>   | <a href="#">SIMATIC S7 Advanced Service Course (based on STEP7 V5.x)</a>                               | 03.26 | Shenyang                         | 8200          |
|                         |                                                                                                        | 05.03 | Shanghai                         |               |
|                         |                                                                                                        | 05.21 | Beijing/Wuhan                    |               |
|                         |                                                                                                        | 03.28 | Chongqing                        |               |
| <a href="#">A7112CP</a> | <a href="#">Test: Siemens Certified Service Technician Level 2</a>                                     | 04.04 | Shenyang                         | 1100          |
|                         |                                                                                                        | 05.12 | Shanghai                         |               |
|                         |                                                                                                        | 05.30 | Wuhan                            |               |
|                         |                                                                                                        | 03.19 | Beijing                          |               |
| <a href="#">A7113</a>   | <a href="#">SIMATIC S7 Advanced Programming Course (based on STEP7 V5.x)</a>                           | 03.26 | Wuhan                            |               |
|                         |                                                                                                        | 04.16 | Shenyang/Chongqing               | 9300          |
|                         |                                                                                                        | 05.02 | Guangzhou                        |               |
|                         |                                                                                                        | 05.14 | Shanghai                         |               |
|                         |                                                                                                        | 03.09 | Beijing                          |               |
| <a href="#">A7113CP</a> | <a href="#">Test: Siemens Certified S7 Programmer</a>                                                  | 04.26 | Shenyang/Chongqing               | 1100          |
|                         |                                                                                                        | 05.12 | Guangzhou                        |               |

|                       |                                                                                |       |                   |      |
|-----------------------|--------------------------------------------------------------------------------|-------|-------------------|------|
|                       |                                                                                | 05.24 | Shanghai          |      |
|                       |                                                                                | 04.02 | Beijing           |      |
| <a href="#">A7122</a> | <a href="#">Design and Programming of SIMATIC S7-300F Distributed Safety</a>   | 05.02 | Shanghai          | 3900 |
|                       |                                                                                | 05.15 | Guangzhou         |      |
|                       |                                                                                | 05.21 | Chongqing         |      |
|                       |                                                                                | 04.08 | Guangzhou         |      |
| <a href="#">A1474</a> | <a href="#">SIMATIC S7 Sequential Control Systems with S7-GRAPH</a>            | 04.23 | Shanghai          | 3750 |
|                       |                                                                                | 05.02 | Beijing           |      |
| <a href="#">A1476</a> | <a href="#">SIMATIC S7 Continuous Function Chart (CFC)</a>                     | 04.09 | Beijing           | 2500 |
| <a href="#">A1480</a> | <a href="#">SIMATIC S7 Programming with SCL</a>                                | 04.11 | Beijing/Guangzhou | 2500 |
| <a href="#">A7415</a> | <a href="#">Process Diagnosis through PDIAG and ProAgent</a>                   | 05.03 | Wuhan             | 2500 |
| <a href="#">A7412</a> | <a href="#">PID Control Fundamentals and Application based on SIMATIC S7</a>   | 05.02 | Beijing           | 3900 |
| <a href="#">A7411</a> | <a href="#">Anti-Electromagnetic Interference Analysis of Control System</a>   | 05.03 | Beijing           | 3200 |
| <a href="#">A7414</a> | <a href="#">SIEMENS RFID System</a>                                            | 05.30 | Wuhan             | 2600 |
| <a href="#">A1172</a> | <a href="#">SIMATIC S7-200/200 CN/200 SMART Micro Automation System Course</a> | 03.26 | Shanghai          | 4500 |

#### SIMATIC NET

| Course ID             | Course Name                                                             | Date  | City                     | Price ( CNY ) |
|-----------------------|-------------------------------------------------------------------------|-------|--------------------------|---------------|
|                       |                                                                         | 03.12 | Beijing                  |               |
|                       |                                                                         | 03.19 | Wuhan/Chongqing          |               |
| <a href="#">A7225</a> | <a href="#">PROFINET/Industrial Ethernet System Course</a>              | 04.23 | Shanghai                 | 5800          |
|                       |                                                                         | 05.21 | Guangzhou                |               |
|                       |                                                                         | 05.28 | Wuhan                    |               |
| <a href="#">A7226</a> | <a href="#">Industrial Wireless LAN System Course</a>                   | 05.30 | Shanghai                 | 2600          |
|                       |                                                                         | 04.23 | Shenyang/Wuhan/Chongqing |               |
| <a href="#">A1497</a> | <a href="#">PROFIBUS Network Service, Maintenance and Field Devices</a> | 05.14 | Beijing                  | 5800          |
|                       |                                                                         | 05.28 | Guangzhou                |               |

#### SIMATIC HMI

| Course ID             | Course Name                                  | Date  | City                       | Price ( CNY ) |
|-----------------------|----------------------------------------------|-------|----------------------------|---------------|
|                       |                                              | 05.03 | Beijing/Shanghai/Guangzhou | 7800          |
| <a href="#">A1479</a> | <a href="#">WinCC System Course</a>          | 05.21 | Shenyang                   |               |
|                       |                                              | 04.16 | Shanghai                   |               |
|                       |                                              | 04.23 | Beijing                    | 5500          |
| <a href="#">A1484</a> | <a href="#">WinCC Flexible System Course</a> | 05.07 | Chongqing                  |               |
|                       |                                              | 05.14 | Guangzhou                  |               |

#### SIMATIC PCS7

| Course ID               | Course Name                                                  | Date  | City           | Price ( CNY ) |
|-------------------------|--------------------------------------------------------------|-------|----------------|---------------|
|                         |                                                              | 03.12 | Shanghai/Wuhan |               |
| <a href="#">A1501</a>   | <a href="#">SIMATIC PCS7 System Course</a>                   | 04.09 | Wuhan          | 11500         |
|                         |                                                              | 05.14 | Shanghai       |               |
|                         |                                                              | 05.21 | Beijing        |               |
| <a href="#">A1501CP</a> | <a href="#">Test: Siemens SIMATIC PCS7 Basic Engineer</a>    | 05.25 | Shanghai       | 600           |
|                         |                                                              | 03.19 | Beijing        | 12500         |
| <a href="#">A1503</a>   | <a href="#">SIMATIC PCS7 Advanced Course</a>                 | 04.09 | Shanghai       |               |
|                         |                                                              | 03.31 | Beijing        | 1100          |
| <a href="#">A1503CP</a> | <a href="#">Test: Siemens Certified PCS7 Engineer</a>        | 04.20 | Shanghai       |               |
| <a href="#">A7121</a>   | <a href="#">Design and Programming with F-System in PCS7</a> | 04.02 | Shanghai       | 4000          |

#### Low Voltage Drive Device

| Course ID             | Course Name                                                                              | Date  | City              | Price ( CNY ) |
|-----------------------|------------------------------------------------------------------------------------------|-------|-------------------|---------------|
| <a href="#">D7400</a> | <a href="#">Basics of drive technology</a>                                               | 03.19 | Beijing           | 5100          |
|                       |                                                                                          | 03.26 | Beijing           |               |
| <a href="#">D7212</a> | <a href="#">SINAMICS S120 Service and Commissioning (servo control)</a>                  | 05.07 | Beijing           | 6200          |
|                       |                                                                                          | 05.28 | Shanghai/Shenyang |               |
| <a href="#">D7226</a> | <a href="#">SINAMICS S120 Service and Commissioning Advanced Course (servo control)</a>  | 03.26 | Shanghai          | 6200          |
|                       |                                                                                          | 05.14 | Beijing           |               |
| <a href="#">D7213</a> | <a href="#">SINAMICS S120 Cabinet Modules Service and Commissioning (vector control)</a> | 03.12 | Beijing           | 6200          |
|                       |                                                                                          | 05.07 | Wuhan             |               |

|                            |                                                                         |       |                    |      |
|----------------------------|-------------------------------------------------------------------------|-------|--------------------|------|
| <a href="#">D7219</a>      | <a href="#">SINAMICS S120 Diagnostics and Service</a>                   | 03.12 | Shanghai/Guangzhou |      |
|                            |                                                                         | 05.07 | Shanghai           | 6200 |
| <a href="#">D7224</a>      | <a href="#">SINAMICS Repair Course</a>                                  | 04.09 | Beijing            | 6800 |
| <a href="#">D7223</a>      | <a href="#">SINAMICS S120 Safety Integrated</a>                         | 04.10 | Shanghai           |      |
|                            |                                                                         | 05.21 | Beijing            | 5000 |
| <a href="#">D7218</a>      | <a href="#">SINAMICS S120 Configuration</a>                             | 04.02 | Shanghai           |      |
|                            |                                                                         | 05.28 | Beijing            | 3900 |
| <a href="#">D7211</a>      | <a href="#">SINAMICS G150/G130/S150 Service and Commissioning</a>       | 04.16 | Beijing            |      |
|                            |                                                                         | 05.21 | Guangzhou          | 6200 |
| <a href="#">D7210</a>      | <a href="#">SINAMICS G120 Commissioning and Service</a>                 | 04.02 | Beijing            |      |
|                            |                                                                         | 04.23 | Shanghai           | 3600 |
| <a href="#">D7227(new)</a> | <a href="#">SINAMICS G120 Commissioning and Service Advanced Course</a> | 04.26 | Shanghai           | 3600 |
| <a href="#">D7111</a>      | <a href="#">SINAMICS DCM Service and Commissioning</a>                  | 04.16 | Shanghai           |      |
|                            |                                                                         | 04.23 | Beijing            | 6200 |
| <a href="#">D2104</a>      | <a href="#">SIMOVERT MASTERDRIVES 6SE70 Service</a>                     | 05.07 | Beijing            | 6200 |
| <a href="#">E2101</a>      | <a href="#">EMC Course for Drive System</a>                             | 04.02 | Beijing            | 3200 |

#### Medium Voltage Drive Device

| Course ID             | Course Name                                             | Date  | City | Price ( CNY ) |
|-----------------------|---------------------------------------------------------|-------|------|---------------|
| <a href="#">D7216</a> | <a href="#">PH Perfect Harmony GH180 Service Course</a> | 03.28 | SED5 | 5000          |
|                       |                                                         | 05.09 |      |               |

#### SINUMERIK CNC Control

| Course ID             | Course Name                                                                  | Date  | City     | Price ( CNY ) |
|-----------------------|------------------------------------------------------------------------------|-------|----------|---------------|
| <a href="#">T8401</a> | <a href="#">SINUMERIK 840D SL Service and Installation</a>                   | 03.12 | Shanghai |               |
|                       |                                                                              | 05.14 |          | 11500         |
|                       |                                                                              | 04.09 | Beijing  |               |
|                       |                                                                              | 05.07 |          |               |
| <a href="#">T8402</a> | <a href="#">SIMATIC S7 for SINUMERIK 840D SL / 840D</a>                      | 04.23 | Beijing  | 5600          |
| <a href="#">T8403</a> | <a href="#">SINUMERIK 840D SL Safety Integrated Configuring and Start-up</a> | 03.26 | Beijing  | 6800          |
|                       |                                                                              | 04.09 | Shanghai |               |
| <a href="#">T8404</a> | <a href="#">SINUMERIK 840D SL Tool Management Basics</a>                     | 03.19 | Beijing  | 6400          |
| <a href="#">A2485</a> | <a href="#">SINUMERIK 840D Advanced Service and Installation</a>             | 04.23 | Beijing  | 6800          |
|                       |                                                                              | 05.28 | Shanghai |               |
| <a href="#">T8281</a> | <a href="#">SINUMERIK 828D Service and Installation</a>                      | 03.26 | Shanghai | 10400         |
|                       |                                                                              | 04.09 | Beijing  |               |
| <a href="#">T8282</a> | <a href="#">SINUMERIK Operate Operation &amp; Programming</a>                | 03.19 | Beijing  | 6000          |
|                       |                                                                              | 04.16 | Shanghai |               |
| <a href="#">A2482</a> | <a href="#">SINUMERIK HMI Advanced Operation &amp; Programming</a>           | 05.21 | Beijing  | 6000          |
| <a href="#">A2489</a> | <a href="#">SINUMERIK 840D SL / 840D NC Advanced Programming</a>             | 05.28 | Beijing  | 6800          |
| <a href="#">A2400</a> | <a href="#">Foundation of Numeric Control</a>                                | 03.26 | Beijing  | 5600          |

#### SIMOTION Motion Control

| Course ID             | Course Name                                 | Date  | City             | Price ( CNY ) |
|-----------------------|---------------------------------------------|-------|------------------|---------------|
| <a href="#">A3101</a> | <a href="#">SIMOTION System Course</a>      | 03.26 | Beijing          |               |
|                       |                                             | 05.07 | Beijing          | 6500          |
|                       |                                             | 05.14 | Shanghai         |               |
| <a href="#">A3102</a> | <a href="#">SIMOTION Programming Course</a> | 05.14 | Beijing          | 6500          |
| <a href="#">A3108</a> | <a href="#">SIMOTION Maintenance Course</a> | 05.21 | Beijing/Shanghai | 6500          |

#### Process Instrumentation & Sensor

| Course ID             | Course Name                                                                                               | Date  | City   | Price ( CNY ) |
|-----------------------|-----------------------------------------------------------------------------------------------------------|-------|--------|---------------|
| <a href="#">P1101</a> | <a href="#">Service for SITRANS P Pressure, SITRANS T Temperature Meter &amp; SIPART Valve Positioner</a> | 04.09 | Dalian | 5100          |
| <a href="#">P1102</a> | <a href="#">Service for SITRANS F Flowmeter</a>                                                           | 04.16 | Dalian | 5100          |
| <a href="#">P1103</a> | <a href="#">Service for SITRANS L Level Meter</a>                                                         | 04.23 | Dalian | 5100          |
| <a href="#">P1104</a> | <a href="#">Siwarex Integration Static Weight Production Training</a>                                     | 03.26 | Dalian | 2600          |
| <a href="#">P1105</a> | <a href="#">Mass Dynamics Production Training</a>                                                         | 03.08 | Dalian | 3800          |
|                       |                                                                                                           | 04.16 |        |               |
| <a href="#">P2101</a> | <a href="#">Maxum II Gas Chromatography</a>                                                               | 05.21 | Dalian | 9000          |

#### Building Control

|  |  |  |  |  |
|--|--|--|--|--|
|  |  |  |  |  |
|--|--|--|--|--|

| Course ID             | Course Name                                                                               | Date  | City      | Price<br>( CNY ) |
|-----------------------|-------------------------------------------------------------------------------------------|-------|-----------|------------------|
| <a href="#">E1002</a> | <a href="#">KNX/EIB Advanced Training in Smart Home and Building Control Applications</a> | 03.12 | Shanghai  | 5250             |
| <a href="#">E1006</a> | <a href="#">APOGEE Building Automation System Programming and Commissioning Course</a>    | 04.16 | Guangzhou | 5300             |

#### Low-Voltage Power Distribution, Control and Protection

| Course ID             | Course Name                                                          | Date  | City     | Price<br>( CNY ) |
|-----------------------|----------------------------------------------------------------------|-------|----------|------------------|
| <a href="#">D3101</a> | <a href="#">SIMOCODE Pro Engineering and Commissioning</a>           | 03.19 | Beijing  | 2200             |
| <a href="#">D3103</a> | <a href="#">Low-Voltage Power Distribution and Monitoring System</a> | 03.21 | Beijing  | 3400             |
|                       |                                                                      | 04.02 | Shanghai |                  |

For more detailed information, please pay attention to training's official website

[www.siemens.com.cn/sitrain](http://www.siemens.com.cn/sitrain)

Training, help individual excellence, achievement enterprise development !