

VASS V6 Upgrade Workshop for OEM (CT-VAS6OEM)

Objectifs

The workshop covers the relevant programming topics of the VASS V6 standard, especially what's new since the previous version (V05), as preparation for certification by Volkswagen AG.
This is a concise expert workshop targeting commissioning engineers of systems in the VASS V6 standard.

Groupes cibles

Commissioning engineers
Configuration engineers
Programmers

Programme / Contenu

Editing projects, country settings, text lists, designations
Project creation, safety specifics for FSEND DP FRCVDP
Differences in blocks compared with VASS 05:
Elimination of bit memory, DB concept
Programming rules in LAD and Graph 7
Rules for generating the visualization
Compiling and error handling
Software tools for SIMATIC Openness: OpnsToolSuite, OpenTopology, LibraryCompare
PROFINET diagnostics of the VASS standard
ProDiag / Alarms
Block help
Introduction to structure of safety program
Generating a safety program
HMI: New features in the faceplates
Settings in SiVArc
Generating a visualization
Manual follow-up work

Prérequis

The following requirement is essential for participation in the VASS V6 Workshop:

- SIMATIC TIA Portal S7-1500 – Proficiency in the use and programming of the S7-1500 CPU as well as programming in the Safety Integrated environment. The required knowledge corresponds to the contents of the TIA-PRO1, TIA-PRO2 or the TIA-SYSUP and TIA-SAFETY courses.
- VASS Standard V05 – Knowledge of the VASS standard and/or project experience in commissioning VASS projects.

Remarque

Notebook:

Please bring your own notebook to the workshop. The installation of disk drives C and D is required.

Please install the following programs (version) before the workshop

- SIMATIC STEP 7 Professional (Version 16 Update 2)
- SIMATIC STEP 7 Safety Advanced (Version 16)
- SIMATIC WinCC Advanced (Version 16 Update 2)
- SIMATIC Visualization Architect (Version 16 Update 2)
- TIA Portal Openness (Version 16 Update 2)
- SIMATIC WinCC Runtime Advanced, 8192 Power Tags (Version 16 Update 2)
- SINAMICS Startdrive (Version 16 Update 2)
- PLCSIM (Version 16 Update 2)

Type

Formation en salle

Durée

2 Jours

Langue

en